



Standard Life PS

300M/IF 120-130V 60PK

Standard Life Incandescent, vacuum or gas-filled lamp has a crystal clear bulb and a completely visible filament, so the brightness of the light is not 'softened.' It imparts a sparkling radiance to larger luminaires and wall brackets with textured or satin-etched glass and cut crystal. It is the appropriate lamp for large luminaires with clear glass bowls, mounted indoors or outdoors. It is recommended in all such cases where brilliance and sparkle are more important than the avoidance of glare. These lamps are also used for indirect lighting in closed luminaires.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	750 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	6,230 lm
Operating and Electrical	
Power Consumption	300 W
Voltage (Nom)	120-130 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	PS25
Product Data	
Order product name	300M/IF 120-130V 60PK
Full product name	300M/IF 120-130V 60PK
Order code	281774
Material Nr. (12NC)	920140834302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677281779
Numerator - Packs per outer box	60
EAN/UPC - Case	50046677281774

Standard Life PS

Dimensional drawing



Product
300M/IF 120-130V 60PK

