



# Rough / Vibration Service

## 75A/RS/VS 120-130V 12/1


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	712 lm
Operating and Electrical	
Power Consumption	75 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	120-130 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A19 [A 19mm]
Product Data	
Order product name	75A/RS/VS 120-130V 12/1
Full product name	75A/RS/VS 120-130V 12/1
Order code	293605
Material Nr. (12NC)	920586334302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677293604
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677293609

Dimensional drawing



A19

Product
75A/RS/VS 120-130V 12/1

