



# Rough / Vibration Service

## 100A/RS 250V 60PK

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	1,030 lumen
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	250 V
Voltage (Nom)	250 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	A21 [A 21mm]
Product Data	
Order product name	100A/RS 250V 60PK
Order code	920647046205
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	60
Material Nr. (12NC)	920647046205
Full product name	100A/RS 250V 60PK
EAN/UPC - Case	50046677275506
EAN/UPC - Product/Case	046677275501

Rough / Vibration Service

Dimensional drawing

Product	D	C (max)
100A/RS 250V 60PK	2.625 inch	5.312 inch

