



# DuraMax Reflector Flood

## 65BR/FL60/LL 120V 8/1 TP

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	H90 [Hanging +/-90D or Base Up HOR (BUH)]
Nominal lifetime	2,500 hour(s)
Rated Lifetime (Hours)	2,500 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	60 degree(s)
Luminous Flux	625 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	65 W
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR40
Product Data	
Order product name	65BR/FL60/LL 120V 8/1 TP
Full product name	65BR/FL60/LL 120V 8/1 TP
Order code	920670136316
Material Nr. (12NC)	920670136316
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677167820
Numerator - Packs per outer box	8
EAN/UPC - Case	50046677167412

## DuraMax Reflector Flood

### Dimensional drawing



#### Product

65BR/FL60/LL 120V 8/1 TP

