



Reflector Flood

500R40/3FL 250V 24/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Operating and Electrical	
Power Consumption	500 W
Voltage (Nom)	250 V
Voltage (Nom)	250 V
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Hard Glass
Bulb Shape	R40 (R40)

Approval and Application	
Approval Marks	Circle E logo
Product Data	
Order product name	500R40/3FL 250V 24/1
Full product name	500R40/3FL 250V 24/1
Order code	920673746202
Material Nr. (12NC)	920673746202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677144357
Numerator - Packs per outer box	24
EAN/UPC - Case	50046677144352

Reflector Flood

Dimensional drawing



Product	D	C (max)
500R40/3FL 250V 24/1	4.838 inch	7.25 inch

