



Standard Lustre P45 clear

230V 15W GLS CLEAR BAYONET CAP


Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	110 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	15 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	230V 15W GLS CLEAR BAYONET CAP
Full product name	230V 15W GLS CLEAR BAYONET CAP
Full product code	890143700208200
Order code	921400544299
Material Nr. (12NC)	921400544299
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8901437002082
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900076615

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
230V 15W GLS CLEAR BAYONET CAP	45 mm	71.5 mm

