



Standard Lustre P45 clear

Stan 15W E27 220-240V P45 CL 1CT/50X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	115 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	15 W
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	Stan 15W E27 220-240V P45 CL 1CT/50X10F
Full product name	Stan 15W E27 220-240V P45 CL 1CT/50X10F
Full product code	871150017374400
Order code	921402443348
Material Nr. (12NC)	921402443348
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500173744
Numerator - Packs per outer box	500
EAN/UPC - Case	8711500235244

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Stan 15W E27 220-240V P45 CL 1CT/50X10F	45 mm	73 mm

