



Standard Lustre P45 frosted

Stan 25W B15 240V P45 FR 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base


Product data

General Information	
Cap-Base	B15 [B15]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 h
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	205 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	Stan 25W B15 240V P45 FR 1CT/10X10F
Full product name	Stan 25W B15 240V P45 FR 1CT/10X10F
Full product code	871150013645900
Order code	921410145538
Material Nr. (12NC)	921410145538
Local order code	LFR25W240VSBC
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500136459
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500241160

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
Stan 25W B15 240V P45 FR 1CT/10X10F	45 mm	76.5 mm

