



Standard Lustre P45 frosted

Stan 25W B22 240V P45 FR 2CT/10 (2X5)

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	210 lumen
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]
Product Data	
Full product code	871829121545500
Order product name	Stan 25W B22 240V P45 FR 2CT/10 (2X5)
Order code	921410645501
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	921410645501
Full product name	Stan 25W B22 240V P45 FR 2CT/10 (2X5)
EAN/UPC - Case	8718291215462
EAN/UPC - Product/Case	8718291215455

Standard Lustre P45 frosted

Dimensional drawing

Product	D	C (max)
Stan 25W B22 240V P45 FR 2CT/10 (2X5)	45 mm	71.5 mm

