



# Standard Lustre P45 frosted

Stan 25W E27 220-240V P45 FR 1CT/5X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

## Product data

| General Information         |                                  |
|-----------------------------|----------------------------------|
| Cap-Base                    | E27 [E27]                        |
| Operating Position          | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime            | 1,000 hour(s)                    |
| Rated Lifetime (Hours)      | 1,000 hour(s)                    |
| Lighting Technology         | Incandescent                     |
| Light Technical             |                                  |
| Luminous Flux               | 200 lm                           |
| Color rendering index (CRI) | 100                              |
| Operating and Electrical    |                                  |
| Power Consumption           | 25 W                             |
| Voltage (Nom)               | 220-240 V                        |
| Controls and Dimming        |                                  |
| Dimmable                    | Yes                              |

| Mechanical and Housing          |  |
|---------------------------------|--|
| Bulb Finish                     | Frosted                                |
| Bulb Shape                      | P45 [P 45mm]                           |
| Product Data                    |  |
| Order product name              | Stan 25W E27 220-240V P45 FR 1CT/5X10F |
| Full product name               | Stan 25W E27 220-240V P45 FR 1CT/5X10F |
| Full product code               | 871829112405400                        |
| Order code                      | 921411643301                           |
| Material Nr. (12NC)             | 921411643301                           |
| Numerator - Quantity Per Pack   | 1                                      |
| EAN/UPC - Product/Case          | 8711500223357                          |
| Numerator - Packs per outer box | 50                                     |
| EAN/UPC - Case                  | 8718291124078                          |

Standard Lustre P45 frosted

Dimensional drawing



| Product                                | D     | C (max) |
|--|-------|---------|
| Stan 25W E27 220-240V P45 FR 1CT/5X10F | 45 mm | 73 mm   |

