



Standard Lustre P45 frosted

Stan 25W E27 220-240V P45 FR 1CT/5X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

Product data

General Information

Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical

Luminous Flux	200 lm
Color rendering index (CRI)	100

Operating and Electrical

Power Consumption	25 W
Voltage (Nom)	220-240 V

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing


Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]

Product Data

Order product name	Stan 25W E27 220-240V P45 FR 1CT/5X10F
Full product name	Stan 25W E27 220-240V P45 FR 1CT/5X10F
Full product code	871829112405400
Order code	921411643301
Material Nr. (12NC)	921411643301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500223357
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291124078

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
Stan 25W E27 220-240V P45 FR 1CT/5X10F	45 mm	73 mm

