



# Standard Lustre P45 frosted

CLAS 25W E27 230V P45 FR 1000H 1CT/10x10

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base


## Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	205 lumen
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]
Product Data	
Full product code	692341076278500
Order product name	CLAS 25W E27 230V P45 FR 1000H 1CT/10x10
Order code	921419244260
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	921419244260
Full product name	CLAS 25W E27 230V P45 FR 1000H 1CT/10x10
EAN/UPC - Case	6923410763713
EAN/UPC - Product/Case	6923410762785

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
CLAS 25W E27 230V P45 FR 1000H 1CT/10x10	45 mm	73 mm

