



Standard Lustre P45 clear

CLAS 40W E27 230V P45 CL 1000H 1CT/10x10

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base


Product data

| General Information | |
|-----------------------------|----------------------------------|
| Cap-Base | E27 [E27] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Luminous Flux | 390 lm |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 40 W |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|--|
| Bulb Finish | Clear |
| Bulb Shape | P45 [P 45mm] |
| Product Data | |
| Order product name | CLAS 40W E27 230V P45 CL 1000H 1CT/10x10 |
| Full product name | CLAS 40W E27 230V P45 CL 1000H 1CT/10x10 |
| Full product code | 692341076279200 |
| Order code | 921419344260 |
| Material Nr. (12NC) | 921419344260 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 6923410762792 |
| Numerator - Packs per outer box | 100 |
| EAN/UPC - Case | 6923410763720 |

Standard Lustre P45 clear

Dimensional drawing



| Product | D | C (max) |
|--|-------|---------|
| CLAS 40W E27 230V P45 CL 1000H 1CT/10x10 | 45 mm | 73 mm |

