



# Standard Lustre P45 frosted

**CLAS 40W E27 230V P45 FR 1000H 1CT/10x10**


Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

## Product data

General Information		Mechanical and Housing	
Cap-Base	E27 [E27]	Bulb Finish	Frosted
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	P45 [P 45mm]
Nominal lifetime	1,000 hour(s)		
Rated Lifetime (Hours)	1,000 hour(s)		
Lighting Technology	Incandescent		
Light Technical		Product Data	
Luminous Flux	390 lumen	Full product code	692341076280800
Color rendering index (CRI)	100	Order product name	CLAS 40W E27 230V P45 FR 1000H 1CT/10x10
		Order code	921419444260
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	40 W	Numerator - Packs per outer box	100
Voltage (Nom)	230 V	Material Nr. (12NC)	921419444260
Voltage (Nom)	230 V	Full product name	CLAS 40W E27 230V P45 FR 1000H 1CT/10x10
		EAN/UPC - Case	6923410763737
		EAN/UPC - Product/Case	6923410762808
Controls and Dimming			
Dimmable	Yes		

## Standard Lustre P45 frosted

### Dimensional drawing



Product	D	C (max)
CLAS 40W E27 230V P45 FR 1000H 1CT/10x10	45 mm	73 mm

