



Standard Lustre P45 clear

Stan 40W E27 125-130V P45 CL 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Product data

General Information		Mechanical and Housing	
Cap-Base	E27 [E27]	Bulb Finish	Clear
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	P45 [P 45mm]
Nominal lifetime	1,000 hour(s)	Product Data	
Rated Lifetime (Hours)	1,000 hour(s)	Order product name	Stan 40W E27 125-130V P45 CL 1CT/10X10F
Lighting Technology	Incandescent	Full product name	Stan 40W E27 125-130V P45 CL 1CT/10X10F
Light Technical		Full product code	871016307607250
Luminous Flux	460 lm	Order code	921421535673
Color rendering index (CRI)	100	Material Nr. (12NC)	921421535673
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	40 W	EAN/UPC - Product/Case	8710163076072
Voltage (Nom)	125-130 V	Numerator - Packs per outer box	100
Controls and Dimming		EAN/UPC - Case	8710163077703
Dimmable	Yes		

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Stan 40W E27 125-130V P45 CL 1CT/10X10F	45 mm	73 mm

