



# Standard Lustre P45 clear

**Stan 40W E27 220-240V P45 CL 1CT/5X10F**

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

## Product data

General Information		Mechanical and Housing	
Cap-Base	E27 [E27]	Bulb Finish	Clear
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	P45 [P 45mm]
Nominal lifetime	1,000 hour(s)	Product Data	
Rated Lifetime (Hours)	1,000 hour(s)	Order product name	Stan 40W E27 220-240V P45 CL 1CT/5X10F
Lighting Technology	Incandescent	Full product name	Stan 40W E27 220-240V P45 CL 1CT/5X10F
Light Technical		Full product code	871829112414600
Luminous Flux	385 lm	Order code	921421543301
Color rendering index (CRI)	100	Material Nr. (12NC)	921421543301
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	40 W	EAN/UPC - Product/Case	8711500223333
Voltage (Nom)	220-240 V	Numerator - Packs per outer box	50
Controls and Dimming		EAN/UPC - Case	8718291124160
Dimmable	Yes		

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Stan 40W E27 220-240V P45 CL 1CT/5X10F	45 mm	73 mm

