



# Softone Lustre T45

## SOFT 40W E27 230V T45 WH 1CT/10X10F

Normal gas-filled incandescent lamps with a T-shaped glass bulb and E-base


### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	350 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Soft White
Bulb Shape	T45 [T 45mm]
Product Data	
Order product name	Soft 40W E27 230V T45 WH 1CT/10X10F
Full product name	SOFT 40W E27 230V T45 WH 1CT/10X10F
Full product code	871150004320750
Order code	04320750
Material Nr. (12NC)	921431744217
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500043207
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500111760

## Softone Lustre T45

### Dimensional drawing



Product	D	C (max)
Soft 40W E27 230V T45 WH 1CT/10X10F	45 mm	74 mm

