



# Reflector diam 80/90/95/125 mm

## Refl 100W B22 230V R95 FR 1SL/25

Normal incandescent lamps with an internal ring-shaped parabolic aluminium mirror behind the filament


### Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	100 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	R95 [R 95mm]
Product Data	
Order product name	Refl 100W B22 230V R95 FR 1SL/25
Full product name	Refl 100W B22 230V R95 FR 1SL/25
Full product code	872790007470300
Order code	923206444299
Material Nr. (12NC)	923206444299
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900074703
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900076585

Reflector diam 80/90/95/125 mm

Dimensional drawing



Product	D	C (max)
Refi 100W B22 230V R95 FR 1SL/25	95 mm	135 mm

