



# Reflector diam 80/90/95/125 mm

## Refl 60W E27 240V E80 80D FR 1CT/6X5F

Normal incandescent lamps with an internal ring-shaped parabolic aluminium mirror behind the filament

### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Beam Angle (Nom)	80 degree(s)
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	E80 [E 80mm]

Product Data	
Order product name	Refl 60W E27 240V E80 80D FR 1CT/6X5F
Full product name	Refl 60W E27 240V E80 80D FR 1CT/6X5F
Full product code	872790081044800
Order code	923226545549
Material Nr. (12NC)	923226545549
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900810448
Numerator - Packs per outer box	30
EAN/UPC - Case	8727900810462

## Reflector diam 80/90/95/125 mm

### Dimensional drawing



Product	D	C (max)
Ref <sup>l</sup> 60W E27 240V E80 80D FR 1CT/6X5F	80 mm	114.5 mm

