



Reflector diam 80/90/95/125 mm

Refl 100W E27 240V E80 80D FR 1CT/6X5F

Normal incandescent lamps with an internal ring-shaped parabolic aluminium mirror behind the filament


Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	80 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	E80 [E 80mm]
Product Data	
Order product name	Refl 100W E27 240V E80 80D FR 1CT/6X5F
Full product name	Refl 100W E27 240V E80 80D FR 1CT/6X5F
Full product code	872790081053000
Order code	923229545526
Material Nr. (12NC)	923229545526
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900810530
Numerator - Packs per outer box	30
EAN/UPC - Case	8727900810554

Reflector diam 80/90/95/125 mm

Dimensional drawing



Product	D	C (max)
Ref 100W E27 240V E80 80D FR 1CT/6X5F	80 mm	114.5 mm

