



Appliance Oven P45

APPL 40W E14 240V P45 CL OV 1CT/10X10F

Lustre vacuum lamps with clear glass (P-bulb)


Product data

General Information	
Cap base	E14 [E14]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 h
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 h
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	420 lm
Correlated Colour Temperature	2700 K
Colour rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40.0 W
Lamp current (nom.)	0.17 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	240 V
Voltage (nom.)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	P45 [P 45 mm]
Approval and Application	
Energy consumption kWh/1,000 hours	40 kWh
Product Data	
Order product name	Appl 40W E14 240V P45 CL OV 1CT/10X10F
Full product name	APPL 40W E14 240V P45 CL OV 1CT/10X10F
Full EOC	871150003545550
Order code	03545550
Material no. (12 NC)	923265945546
Local order code	40SESOZ
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500035455
Numerator – packs per outer box	100
EAN/UPC - Case	8711500085221

Appliance Oven P45

Dimensional drawing



Product	D	C (max)
Appl 40W E14 240V P45 CL OV 1CT/10X10F	45 mm	75 mm

