



Appliance Oven P45

Appl 40W E14 240V P45 CL OV 1CT/10X10F

Lustre vacuum lamps with clear glass (P-bulb)


Product data

| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | E14 [E14] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Switching Cycle | 4,000 |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Luminous Flux | 420 lm |
| Correlated Color Temperature (Nom) | 2700 K |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 40.0 W |
| Lamp Current (Nom) | 0.17 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 240 V |
| Voltage (Nom) | 240 V |

| Controls and Dimming | |
|---------------------------------|--|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | P45 [P 45mm] |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 40 kWh |
| Product Data | |
| Order product name | Appl 40W E14 240V P45 CL OV 1CT/10X10F |
| Full product name | Appl 40W E14 240V P45 CL OV 1CT/10X10F |
| Full product code | 871150003545550 |
| Order code | 923265945546 |
| Material Nr. (12NC) | 923265945546 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500035455 |
| Numerator - Packs per outer box | 100 |
| EAN/UPC - Case | 8711500085221 |

Appliance Oven P45

Dimensional drawing



| Product | D | C (max) |
|--|-------|---------|
| Appl 40W E14 240V P45 CL OV 1CT/10X10F | 45 mm | 75 mm |

