



# DuraMax Reflector Flood

## 30R20/LL 120V 4/3 TP

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.


### Product data

| General Information      |                                   |
|--------------------------|-----------------------------------|
| Cap-Base                 | E26 [Single Contact Medium Screw] |
| Operating Position       | UNIVERSAL [Any or Universal (U)]  |
| Lighting Technology      | Incandescent                      |
| Operating and Electrical |                                   |
| Power Consumption        | 30 W                              |
| Voltage (Nom)            | 120 V                             |
| Voltage (Nom)            | 120 V                             |
| Mechanical and Housing   |                                   |
| Bulb Finish              | Reflector                         |
| Bulb Shape               | R20 [R 63mm]                      |

| Product Data                    |                      |
|---------------------------------|----------------------|
| Order product name              | 30R20/LL 120V 4/3 TP |
| Full product name               | 30R20/LL 120V 4/3 TP |
| Order code                      | 223131               |
| Material Nr. (12NC)             | 923304736314         |
| Numerator - Quantity Per Pack   | 1                    |
| EAN/UPC - Product/Case          | 046677223137         |
| Numerator - Packs per outer box | 4                    |
| EAN/UPC - Case                  | 50046677223132       |

DuraMax Reflector Flood

Dimensional drawing



| Product              |
|----------------------|
| 30R20/LL 120V 4/3 TP |

