



Reflector diam 39 mm

STD 30W 240V R39 E14 FR 1CT/12

Reflector lamps based on advanced spotlighting technology


Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	45 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	30 W
Voltage (Nom)	240-250 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	R39 [R 39mm]
Product Data	
Order product name	STD 30W 240V R39 E14 FR 1CT/12
Full product name	STD 30W 240V R39 E14 FR 1CT/12
Full product code	871829122509600
Order code	923319045702
Material Nr. (12NC)	923319045702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291225096
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291225102

Reflector diam 39 mm

Dimensional drawing



Product	D	C (max)
STD 30W 240V R39 E14 FR 1CT/12	39 mm	67 mm

