



SPOTONE Ring Mirror Spotline

SPOT 60W B22 240V NR63 30D FR 1CT/6

Reflector lamps based on advanced spotlighting technology


Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63 [NR 63mm]
Product Data	
Order product name	SPOT 60W B22 240V NR63 30D FR 1CT/6
Full product name	SPOT 60W B22 240V NR63 30D FR 1CT/6
Full product code	871150004369610
Order code	923339545583
Material Nr. (12NC)	923339545583
Local order code	R63SP60W240VBC
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500043696
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163071947


SPOTONE Ring Mirror Spotline

Dimensional drawing



Product	D
SPOT 60W B22 240V NR63 30D FR 1CT/6	63 mm

Photometric data



Light Distribution Diagram - SPOT 60W B22 240V NR63 30D FR 1CT/6

