



Infrared Lamps Industrial Use

PAR38 IR 175W E27 240V CL 1CT/12

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, but also food. These benefits have made farmers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data


| General Information | |
|--------------------------|----------------------------------|
| Cap-Base | E27 |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 5,000 hour(s) |
| Rated Lifetime (Hours) | 5,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Color Designation | C |
| Operating and Electrical | |
| Power Consumption | 175 W |
| Voltage (Nom) | 240 V |
| Voltage (Nom) | 240 V |

| Controls and Dimming | |
|-------------------------------|----------------------------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Material | Hard Glass |
| Bulb Shape | PAR38 |
| Product Data | |
| Order product name | PAR38 IR 175W E27 240V CL 1CT/12 |
| Full product name | PAR38 IR 175W E27 240V CL 1CT/12 |
| Full product code | 871150012895915 |
| Order code | 923801345506 |
| Material Nr. (12NC) | 923801345506 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500128959 |

Infrared Lamps Industrial Use

| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 8727900207293 |

Dimensional drawing



| Product | D | C (max) | C1 (max) |
|----------------------------------|--------|---------|----------|
| PAR38 IR 175W E27 240V CL 1CT/12 | 121 mm | 136 mm | 124 mm |

