



PAR56

PAR56 300W MULTIPURPOSE 12V UW 1CT/8

Extremely powerful pressed-glass 179 mm diameter reflector lamps


Product data

General Information	
Cap-Base	MULTIPURPOSE [AKA:Screw Terminal]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	40 degree(s)
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	4,378 lm
Operating and Electrical	
Power Consumption	300.0 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR56 [PAR 7inch/180mm]
Approval and Application	
Energy Consumption kWh/1000 h	318 kWh
Product Data	
Order product name	PAR56 300W Multipurpose 12V UW 1CT/8
Full product name	PAR56 300W MULTIPURPOSE 12V UW 1CT/8
Full product code	871150015969442
Order code	15969442
Material Nr. (12NC)	923804817121
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500159694
Numerator - Packs per outer box	8
EAN/UPC - Case	8711500159700

PAR56

Dimensional drawing



Product	D (max)	C (max)	C1
PAR56 300W Multipurpose 12V UW 1CT/8	178.5 mm	119.3 mm	98 mm

