



PAR38

PAR38 80W E27 240V PAR38 Flood 1CT/6

Pressed-glass 121 mm diameter reflector lamps of high luminous intensity

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2.000 hour(s)
Rated Lifetime (Hours)	2.000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	80 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Product Data	
Order product name	PAR38 80W E27 240V PAR38 Flood 1CT/6
Full product name	PAR38 80W E27 240V PAR38 Flood 1CT/6
Full product code	871150001856497
Order code	923810545580
Material Nr. (12NC)	923810545580
Local order code	PAR38FL80W240V
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500018564
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163073439


PAR38

Dimensional drawing



Product	D	C (max)
PAR38 80W E27 240V PAR38 Flood 1CT/6	122.5 mm	137 mm

Photometric data



Light Distribution Diagram - PAR38 80W E27 240V PAR38 Flood 1CT/6

