



# Halogen High Voltage DE

## PF801 R 1000W R7s 230V 1CT/10

The high, constant light output and consistent color temperature of these double ended high voltage halogen lamps ensure attractive, accurately exposed pictures for both film and video. In addition, the wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.


### Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	15 hour(s)
Operating and Electrical	
Power Consumption	1,000 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Order product name	PF801 R 1000W R7s 230V 1CT/10
Full product name	PF801 R 1000W R7s 230V 1CT/10
Full product code	871150049199225
Order code	923862743201
Material Nr. (12NC)	923862743201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500491992
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500521804

# Halogen High Voltage DE

## Dimensional drawing



Product	D (max)	W	A	C (max)
PF801 R 1000W R7s 230V 1CT/10	9 mm	72 mm	121.7 mm	125.1 mm

