



Halogen High Voltage DE

PF801 R 1000W R7s 230V 1CT/10

The high, constant light output and consistent color temperature of these double ended high voltage halogen lamps ensure attractive, accurately exposed pictures for both film and video. In addition, the wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.


Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	15 hour(s)
Operating and Electrical	
Power Consumption	1,000 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Full product code	871150049199225
Order product name	PF801 R 1000W R7s 230V 1CT/10
Order code	923862743201
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	923862743201
Full product name	PF801 R 1000W R7s 230V 1CT/10
EAN/UPC - Case	8711500521804
EAN/UPC - Product/Case	8711500491992

Halogen High Voltage DE

Dimensional drawing



Product	D (max)	W	A	C (max)
PF801 R 1000W R7s 230V 1CT/10	9 mm	72 mm	121.7 mm	125.1 mm

