



# Halogen High Voltage SE (Theater)

6998P 650W GX9.5 230V 1CT/10

Two distinctive features make this lamp ideal for use in theater luminaires where long life is essential. Firstly, the filament is especially designed for extended lifetime. Secondly the highly innovative P3 technology, developed by Philips, allows the pinch to better withstand extreme heat conditions which extends the average lamp lifetime, ensures consistent high-quality light output over time, and results in fewer early failures and fewer maintenance man hour costs.

## Product data

General Information	
Cap-Base	GX9.5 [GX9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	900 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Operating and Electrical	
Power Consumption	650 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Full product code	871150018487025
Order product name	6998P 650W GX9.5 230V 1CT/10
Order code	923865043228
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	923865043228
Full product name	6998P 650W GX9.5 230V 1CT/10
EAN/UPC - Case	8711500184887
EAN/UPC - Product/Case	8711500184870

# Halogen High Voltage SE (Theater)

## Dimensional drawing

Product	D (max)	H	W	L	C (max)
6998P 650W GX9.5 230V 1CT/10	22 mm	12.5 mm	10 mm	55 mm	110 mm

