



Halogen High Voltage SE (Theater)

6996P 1000W GX9.5 230V 1CT/10

Two distinctive features make this lamp ideal for use in theater luminaires where long life is essential. Firstly, the filament is especially designed for extended lifetime. Secondly the highly innovative P3 technology, developed by Philips, allows the pinch to better withstand extreme heat conditions which extends the average lamp lifetime, ensures consistent high-quality light output over time, and results in fewer early failures and fewer maintenance man hour costs.


产品数据

一般信息	
底盖	GX9.5 [GX9.5]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	900 小时
操作和电气	
功耗	1,000 W
电压 (标称)	230 V
电压 (标称)	230 V
控制和调光	
可调光	是
机械和外壳	
灯泡外观	透明

产品数据	
订单产品名称	6996P 1000W GX9.5 230V 1CT/10
完整的产品名称	6996P 1000W GX9.5 230V 1CT/10
完整产品代码	871150018493125
订购代码	923865143228
材料编号 (12NC)	923865143228
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500184931
计算器 - 每个外包装箱中的包数	10
EAN/UPC - 案例	8711500184948

Halogen High Voltage SE (Theater)

二维绘图



Product	D (max)	H	W	L	C (max)
6996P 1000W GX9.5 230V 1CT/10	23 mm	17 mm	11 mm	55 mm	110 mm

