



Halogen High Voltage SE (Theater)

6996P 1000W GX9.5 240V 1CT/10

Two distinctive features make this lamp ideal for use in theater luminaires where long life is essential. Firstly, the filament is especially designed for extended lifetime. Secondly the highly innovative P3 technology, developed by Philips, allows the pinch to better withstand extreme heat conditions which extends the average lamp lifetime, ensures consistent high-quality light output over time, and results in fewer early failures and fewer maintenance man hour costs.


Product data

| General Information | |
|----------------------------|----------------------------------|
| Cap-Base | GX9.5 [GX9.5] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Life to 50% Failures (Nom) | 900 h |
| Operating and Electrical | |
| Power Consumption | 1,000 W |
| Voltage (Nom) | 240 V |
| Voltage (Nom) | 240 V |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |

| Product Data | |
|---------------------------------|-------------------------------|
| Order product name | 6996P 1000W GX9.5 240V 1CT/10 |
| Full product name | 6996P 1000W GX9.5 240V 1CT/10 |
| Full product code | 871150018496225 |
| Order code | 923865145528 |
| Material Nr. (12NC) | 923865145528 |
| Local order code | 6996P240V |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500184962 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8711500184979 |

Halogen High Voltage SE (Theater)

Dimensional drawing



| Product | D (max) | H | W | L | C (max) |
|-------------------------------|---------|-------|-------|-------|---------|
| 6996P 1000W GX9.5 240V 1CT/10 | 23 mm | 17 mm | 11 mm | 55 mm | 110 mm |

