



Halogen non-reflector

6550 150W G6.35 15V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


Product data

| General Information | |
|------------------------------------|--|
| Cap-Base | G6.35 [G6.35] |
| Operating Position | S90 [Standing +/-90D or Base Down (BDH)] |
| Life to 50% Failures (Nom) | 50 hour(s) |
| Light Technical | |
| Correlated Color Temperature (Nom) | 3450 K |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 150 W |
| Voltage (Nom) | 15 V |
| Voltage (Nom) | 15 V |
| Mechanical and Housing | |
| Bulb Material | Quartz-UV Open |

| Product Data | |
|---------------------------------|--------------------------------|
| Order product name | 6550 150W G6.35 15V 1CT/10X10F |
| Full product name | 6550 150W G6.35 15V 1CT/10X10F |
| Full product code | 871150040984350 |
| Order code | 40984350 |
| Material Nr. (12NC) | 923870618503 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500409843 |
| Numerator - Packs per outer box | 100 |
| EAN/UPC - Case | 8711500423184 |

Halogen non-reflector

Dimensional drawing



| Product | D (max) | L (min) | L (max) | L | P (max) | P | P (min) | C (max) |
|------------|---------|---------|---------|----|---------|------|---------|---------|
| 6550 150W | 11.5 mm | 29.75 | 30.25 | 30 | 1.05 mm | 1 mm | 0.95 | 44 mm |
| G6.35 15V | | mm | mm | mm | | | mm | |
| 1CT/10X10F | | | | | | | | |

