



Halogen non-reflector

7388 20W G4 6V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


产品数据

一般信息	
底盖	G4 [G4]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	100 小时
灯技术	
光通量	460 lm
显色指数 (CRI)	100
操作和电气	
功耗	20 W
电压 (标称)	6 V
电压 (标称)	6 V
机械和外壳	
灯泡材料	开放紫外线石英

产品数据	
订单产品名称	7388 20W G4 6V 1CT/10X10F
完整的产品名称	7388 20W G4 6V 1CT/10X10F
完整产品代码	871150040986750
订购代码	923874610103
材料编号 (12NC)	923874610103
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500409867
计算器 - 每个外包装箱中的包数	100
EAN/UPC - 案例	8711500423306

Halogen non-reflector

二维绘图



Product	D (max)	L (max)	C (max)
7388 20W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm

