



# Plusline Large

## Plusline L 500W 240-250V CL 1SL/4X50CT

Mains-voltage linear lamp giving white halogen light


### Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	8,900 lm
Operating and Electrical	
Power Consumption	500 W
Voltage (Nom)	240-250 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	T37 [T 37mm]
Product Data	
Order product name	Plusline L 500W 240-250V CL 1SL/4X50CT
Full product name	Plusline L 500W 240-250V CL 1SL/4X50CT
Full product code	890143700336200
Order code	923880345799
Material Nr. (12NC)	923880345799
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8901437003362
Numerator - Packs per outer box	200
EAN/UPC - Case	8727900076721

# Plusline Large

## Dimensional drawing



Product	D (max)	C (max)
Plusline L 500W 240-250V CL 1SL/4X50CT	12.75 mm	185.7 mm

