



Halogen High Voltage SE (Film/Studio)

6995Z 1000W G22 230V 1CT/10

The high, constant output and consistent color temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. Furthermore, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.


产品数据

一般信息	
底盖	G22 [G22]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	240 小时
灯技术	
相关色温 (标称)	3200 K
操作和电气	
功耗	1,000 W
电压 (标称)	230 V
电压 (标称)	230 V
控制和调光	
可调光	是

机械和外壳	
灯泡外观	透明
产品数据	
订单产品名称	6995Z 1000W G22 230V 1CT/10
完整的产品名称	6995Z 1000W G22 230V 1CT/10
完整产品代码	87115001856525
订购代码	923884742928
材料编号 (12NC)	923884742928
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500185655
计算器 - 每个外包装箱中的包数	10
EAN/UPC - 案例	8711500185662

Halogen High Voltage SE (Film/Studio)

二维绘图



Product	D	H	W	L	C	P	P	R	K	K
	(max)				(max)	(max)	(min)		(max)	(min)
6995Z	28 mm	14.5	11	63.5	140	6.40	6.30	22.22	26.54	24.89
1000W		mm	mm	mm	mm	mm	mm	mm	mm	mm
G22 230V										
1CT/10										

