



Halogen High Voltage SE (Film/Studio)

6995Z 1000W G22 240V 1CT/10

Halogen High Voltage SE (Film/Studio) – stars on film and video The high, constant output and consistent colour temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. What’s more, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.


Product data

| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | G22 [G22] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Life to 50% Failures (Nom) | 240 h |
| Light Technical | |
| Correlated Color Temperature (Nom) | 3200 K |
| Operating and Electrical | |
| Power Consumption | 1,000 W |
| Voltage (Nom) | 240 V |
| Voltage (Nom) | 240 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|-----------------------------|
| Bulb Finish | Clear |
| Product Data | |
| Order product name | 6995Z 1000W G22 240V 1CT/10 |
| Full product name | 6995Z 1000W G22 240V 1CT/10 |
| Full product code | 871150018568625 |
| Order code | 923884745528 |
| Material Nr. (12NC) | 923884745528 |
| Local order code | 6995Z240V |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500185686 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8711500185693 |

Halogen High Voltage SE (Film/Studio)

Dimensional drawing



| Product | D | H | W | L | C | P | P | R | K | K |
|----------|-------|------|----|------|-------|-------|-------|-------|-------|-------|
| | (max) | | | | (max) | (max) | (min) | | (max) | (min) |
| 6995Z | 28 mm | 14.5 | 11 | 63.5 | 140 | 6.40 | 6.30 | 22.22 | 26.54 | 24.89 |
| 1000W | | mm | mm | mm | mm | mm | mm | mm | mm | mm |
| G22 240V | | | | | | | | | | |
| 1CT/10 | | | | | | | | | | |

