



# Halogen High Voltage SE (Theater)

## 6820P 500W GY9.5 230V 1CT/10

Two distinctive features make this lamp ideal for use in theater luminaires where long life is essential. Firstly, the filament is especially designed for extended lifetime. Secondly the highly innovative P3 technology, developed by Philips, allows the pinch to better withstand extreme heat conditions which extends the average lamp lifetime, ensures consistent high-quality light output over time, and results in fewer early failures and fewer maintenance man hour costs.

### Product data

General Information	
Cap-Base	GY9.5 [GY9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	360 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Operating and Electrical	
Power Consumption	500 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Full product code	871150018460325
Order product name	6820P 500W GY9.5 230V 1CT/10
Order code	923894043228
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	923894043228
Full product name	6820P 500W GY9.5 230V 1CT/10
EAN/UPC - Case	8711500184610
EAN/UPC - Product/Case	8711500184603

# Halogen High Voltage SE (Theater)

## Dimensional drawing

Product	D (max)	H	W	L	C (max)
6820P 500W GY9.5 230V 1CT/10	22 mm	11 mm	11 mm	46.5 mm	90 mm

