



HalogenA IDE

HaIA IDE 500W E40 230V CL 1CT/6

Mains-voltage high-wattage double-envelope giving a white halogen light


Product data

| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | E40 |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2,000 hour(s) |
| Switching Cycle | 8,000 |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Halogen |
| Light Technical | |
| Luminous Flux | 10,250 lm |
| Correlated Color Temperature (Nom) | 2900 K |
| Luminous Efficacy (rated) (Nom) | 20.5 lm/W |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 500.0 W |
| Lamp Current (Nom) | 2.17 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |

| Controls and Dimming | |
|---------------------------------|---------------------------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | T38 |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 500 kWh |
| Product Data | |
| Order product name | HaIA IDE 500W E40 230V CL 1CT/6 |
| Full product name | HaIA IDE 500W E40 230V CL 1CT/6 |
| Full product code | 871150049126810 |
| Order code | 923900144240 |
| Material Nr. (12NC) | 923900144240 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500491268 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8711500499943 |

HalogenA IDE

Dimensional drawing



| Product | D (max) | C (max) |
|---------------------------------|---------|---------|
| HalA IDE 500W E40 230V CL 1CT/6 | 38.5 mm | 216 mm |

