



Plusline Compact

Plusline C 100W R7s 240V 1BC/10

Mains-voltage linear lamp giving white halogen light


Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 h
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen
Light Technical	
Luminous Flux	1,550 lm
Luminous Efficacy (rated) (Nom)	15.5 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Lamp Current (Nom)	0.42 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]
Product Data	
Order product name	Plusline C 100W R7s 240V 1BC/10
Full product name	Plusline C 100W R7s 240V 1BC/10
Full product code	871150090173625
Local code description	DECOMP100WB
Order code	923920045792
Material Nr. (12NC)	923920045792
Local order code	DECOMP100W240V
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500901736
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500901781

Plusline Compact

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline C 100W R7s 240V 1BC/10	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

