



# Halogen reflector

## ELH 300W 120V 24PK

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.


### Product data

General Information	
Cap-Base	GY5.3 [GY5.3]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	35 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	300 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Facetted reflector
Product Data	
Order product name	13096 ELH 300W GY5.3 120V 1CT/24
Full product name	ELH 300W 120V 24PK
Full product code	871150041057330
Order code	316190
Material Nr. (12NC)	923920936394
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410573
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500419057

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
13096 ELH 300W GY5.3 120V 1CT/24	2 inch	1-3/4 inch

