



# Halogen reflector

## 13095 250W GY5.3 120V 1CT/24

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

### Product data

General Information	
Cap-Base	GY5.3 [GY5.3]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	175 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	250 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Facetted reflector
Product Data	
Order product name	13095 250W GY5.3 120V 1CT/24
Full product name	13095 250W GY5.3 120V 1CT/24
Full product code	871150041062730
Order code	923921536394
Material Nr. (12NC)	923921536394
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410627
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500419064

# Halogen reflector

## Dimensional drawing



Product	D (max)	C (max)
13095 250W GY5.3 120V 1CT/24	50.7 mm	44.5 mm

