



Plusline Large (double ended)

Plusline Large 1000W R7s 230V 1CT/10


Mains-voltage linear with a coiled-coil filament, giving white halogen light

Product data

General Information		Controls and Dimming	
Cap-Base	R7s	Dimmable	Yes
Operating Position	P4 [Parallel +/-4D or Horizontal(HOR)]	Mechanical and Housing	
Nominal lifetime	2,000 hour(s)	Bulb Finish	Clear
Switching Cycle	8,000	Bulb Shape	T11
Rated Lifetime (Hours)	2,000 hour(s)	Approval and Application	
Lighting Technology	Halogen	Energy Consumption kWh/1000 h	1000 kWh
Light Technical		Product Data	
Luminous Flux	21,500 lm	Order product name	Plusline L 1000W R7s 230V 1CT/10
Correlated Color Temperature (Nom)	2900 K	Full product name	Plusline Large 1000W R7s 230V 1CT/10
Luminous Efficacy (rated) (Nom)	21.5 lm/W	Full product code	871150049434401
Color rendering index (CRI)	100	Order code	49434401
Operating and Electrical		Material Nr. (12NC)	923932143203
Power Consumption	1,000 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	4.35 A	EAN/UPC - Product/Case	8711500494344
Starting Time (Nom)	0.0 s	Numerator - Packs per outer box	10
Warm-up time to 60% light	instant full light s	EAN/UPC - Case	8718291720812
Power Factor (Fraction)	1		
Voltage (Nom)	230 V		
Voltage (Nom)	230 V		

Plusline Large (double ended)

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1000W R7s 230V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm

