



# Plusline Large (double ended)

## PLUS PRO L 1500W R7s 220-230V 1CT/10

PlusLine Large flood delivers maximum light output to light up large areas like outdoor, buildings and shops.

### Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	P4 [Parallel +/-4D or Horizontal(HOR)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	33,000 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	22 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	1,500.0 W
Lamp Current (Nom)	6.52 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11 [T 11mm]

Approval and Application	
Energy Consumption kWh/1000 h	1500 kWh

Product Data	
Order product name	PLUS PRO L 1500W R7s 220-230V 1CT/10
Full product name	PLUS PRO L 1500W R7s 220-230V 1CT/10
Full product code	872790088128800
Order code	923932243205
Material Nr. (12NC)	923932243205
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900881288
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900881295

Plusline Large (double ended)

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
PLUS PRO L 1500W R7s 220-230V 1CT/10	11 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm

