



Plusline Large

Plusline L 1500W R7s 230V 1CT/10

Mains-voltage linear lamp giving white halogen light


Product data

| General Information | |
|------------------------------------|--|
| Cap-Base | R7s |
| Operating Position | P4 [Parallel +/-4D or Horizontal(HOR)] |
| Nominal lifetime | 2,000 hour(s) |
| Switching Cycle | 8,000 |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Halogen |
| Light Technical | |
| Luminous Flux | 33,000 lm |
| Correlated Color Temperature (Nom) | 2900 K |
| Luminous Efficacy (rated) (Nom) | 22 lm/W |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 1,500.0 W |
| Lamp Current (Nom) | 6.52 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |

| Controls and Dimming | |
|---------------------------------|----------------------------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | T11 |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 1500 kWh |
| Product Data | |
| Order product name | Plusline L 1500W R7s 230V 1CT/10 |
| Full product name | Plusline L 1500W R7s 230V 1CT/10 |
| Full product code | 872790080857500 |
| Order code | 923932243241 |
| Material Nr. (12NC) | 923932243241 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8727900808575 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8727900808582 |

Plusline Large

Dimensional drawing



| Product | D (max) | B (max) | B | B (min) | C (max) |
|----------------------------------|---------|----------|----------|----------|----------|
| Plusline L 1500W R7s 230V 1CT/10 | 11 mm | 252.3 mm | 250.7 mm | 249.1 mm | 254.1 mm |

