



# Double Ended Linear

## Double Ended Linear 1500T3Q/P/CL 240V 12PK

High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.


### Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	P4 [Parallel +/-4D or Horizontal(HOR)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	33,000 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	22 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	1,500.0 W
Lamp Current (Nom)	6.25 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	240 V
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11 [T 11mm]
Approval and Application	
Energy Consumption kWh/1000 h	1500 kWh
Product Data	
Order product name	1500T3Q/P/CL 240V 12PK
Full product name	Double Ended Linear 1500T3Q/P/CL 240V 12PK
Order code	132266
Material Nr. (12NC)	923932245793
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677132262
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677132267

Double Ended Linear

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
1500T3Q/P/CL 240V 12PK	7/16 inch	9-15/16 inch	9-7/8 inch	9-13/16 inch	10-1/16 inch

