



Double Ended Linear

1500T3Q/P/CL 240V 12PK

High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.


Product data

| General Information | |
|------------------------------------|--|
| Cap-Base | R7S [R7s] |
| Operating Position | P4 [Parallel +/-4D or Horizontal(HOR)] |
| Nominal lifetime | 2,000 hour(s) |
| Switching Cycle | 8,000 |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Halogen |
| Light Technical | |
| Luminous Flux | 33,000 lumen |
| Correlated Color Temperature (Nom) | 2900 K |
| Luminous Efficacy (rated) (Nom) | 22 lm/W |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 1,500.0 W |
| Lamp Current (Nom) | 6.25 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 240 V |
| Voltage (Nom) | 240 V |

| Controls and Dimming | |
|---------------------------------|------------------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | T11 [T 11mm] |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 1500 kWh |
| Product Data | |
| Order product name | 1500T3Q/P/CL 240V 12PK |
| Order code | 923932245793 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 12 |
| Material Nr. (12NC) | 923932245793 |
| Full product name | 1500T3Q/P/CL 240V 12PK |
| EAN/UPC - Case | 50046677132267 |
| EAN/UPC - Product/Case | 046677132262 |

Double Ended Linear

Dimensional drawing



| Product | D (max) | B (max) | B | B (min) | C (max) |
|------------------------|---------|----------|----------|----------|----------|
| 1500T3Q/P/CL 240V 12PK | 11 mm | 252.3 mm | 250.7 mm | 249.1 mm | 254.1 mm |

