



Broadway Studio/Film monoculot

6874P 300W GY9.5 230V 1CT/10

Two distinctive features make this lamp ideal for use in theater luminaires where long life is essential. Firstly, the filament is especially designed for extended lifetime. Secondly the highly innovative P3 technology, developed by Philips, allows the pinch to better withstand extreme heat conditions which extends the average lamp lifetime, ensures consistent high-quality light output over time, and results in fewer early failures and fewer maintenance man hour costs.

Données du produit

Informations générales	
Culot	GY9.5 [GY9.5]
Position de fonctionnement	UNIVERSEL [Libre ou universelle (U)]
Durée de vie à 50 % de mortalité (nom.)	2 000 h

Fonctionnement et électricité	
Consommation électrique	300 W
Tension (nom.)	230 V
Tension (nom.)	230 V


Commandes et gradation	
Variation de l'intensité lumineuse	Oui

Mécanique et boîtier	
Finition ampoule	Transparent

Données du produit	
Nom du produit de la commande	6874P 300W GY9.5 230V 1CT/10
Nom de produit complet	6874P 300W GY9.5 230V 1CT/10
Code EOC	871150018779625
Code de commande	18779625
Code 12NC	923949743228
Quantité par pack	1
Code EAN – Produit/Boîte	8711500187796
Conditionnement par carton	10
Codes EAN/UPC – Boîte	8711500187819

Broadway Studio/Film monoculot

Schéma dimensionnel



Product	D (max)	H	W	L	C (max)
6874P 300W GY9.5 230V 1CT/10	18 mm	14 mm	8 mm	46,5 mm	80 mm

