



ALR 37/56 mm

GBE 20W 12V 18DEG 50PK

Delivers high lumen output and excellent color rendering for precise accent and display lighting. Philips Halogen Aluminum Reflector Lamps provide continuous color and high luminous intensity for precise accent and display lighting. These lamps offer a rated average life ranging from 2000 hours and feature excellent beam qualities for accent or ambient lighting.

Product data

General Information	
Cap-Base	BA15D [BA15d]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Beam Angle (Nom)	18 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	20.0 W
Lamp Current (Nom)	1.67 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	R37 [R 37mm]

Product Data	
Order product name	GBE 20W DC Bay 12V 18D FR 1CT
Full product name	GBE 20W 12V 18DEG 50PK
Order code	340026
Material Nr. (12NC)	924007717119
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677340025
Numerator - Packs per outer box	50
EAN/UPC - Case	50046677340020


ALR 37/56 mm

Dimensional drawing



Product	D (max)	C (max)
GBE 20W DC Bay 12V 18D FR 1CT	38 mm	41 mm

Photometric data



Light Distribution Diagram - GBE 20W DC Bay 12V 18D FR 1CT

